

AXIS P3225-LV Mk II Network Camera

Streamlined HDTV 1080p fixed dome for any light conditions

AXIS P3225-LV Mk II is a streamlined fixed dome that provides HDTV 1080p video. It features a varifocal lens and remote zoom and focus, which eliminates the need for hands-on fine tuning. Equipped with WDR – Forensic Capture to handle scenes with strong variations in light, Lightfinder technology for exceptional light sensitivity, as well as built-in IR illumination with OptimizedIR, this versatile camera provides outstanding video quality in any light conditions. It supports Axis Zipstream technology that significantly reduces bandwidth and storage requirements.

- > HDTV 1080p video quality
- > Remote zoom and focus
- > Lightfinder and WDR Forensic Capture
- > OptimizedIR illumination
- > Axis Zipstream







AXIS P3225-LV Mk II Network Camera

Camera	2 1 22 21 22 12 2	
Image sensor	Progressive scan RGB CMOS 1/3"	
Lens	Varifocal, 3.0–10.5 mm, F1.4 Horizontal field of view: 92°-34°	
	Vertical field of view: 52 –54 Vertical field of view: 50°–20°	Data stre
	Remote focus and zoom, P-Iris control, IR corrected	Built-in
Day and night	Automatically removable infrared-cut filter	installati
Minimum	HDTV 1080p 25/30 fps with WDR - forensic capture and	General
illumination	Lightfinder: Color: 0.16 lux at 50 IRE, F1.4 B/W: 0.03 lux at 50 IRE, F1.4, 0 lux with IR illumination on HDTV 1080p 50/60 fps: Color: 0.32 lux at 50 IRE, F1.4 B/W: 0.06 lux at 50 IRE, F1.4, 0 lux with IR illumination on	Casing
Shutter time	1/66500 s to 1 s	Sustainal
Camera angle adjustment	Pan ±180°, tilt -35 to +75°, rotation ±95°	Memory Power
Video		
Video compression	H.264 Baseline, Main and High Profile (MPEG-4 Part 10/AVC) Motion JPEG	Connecto IR illumin
Resolution	1920x1080 to 160x90	
Frame rate	With WDR: 25/30 fps with power line frequency 50/60 Hz Without WDR: 50/60 fps with power line frequency 50/60 Hz	Storage
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG	
	Axis Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264	Operating condition
Multi-view streaming	2 individually cropped out view areas	Storage condition
Pan/Tilt/Zoom	Digital PTZ, preset positions	Approval
lmage settings	Compression, Color, Brightness, Sharpness, Contrast, Local contrast, White balance, Exposure control (including automatic gain control), Exposure zones, Fine tuning of behavior at different light levels, WDR - forensic capture: Up to 120 dB depending on scene, Text and image overlay, Mirroring of images, Privacy masks Rotation: 0°, 90°, 180°, 270°, including Corridor Format	
Network		
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized Certificate Management	
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMP v1/v2c/v3(MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SRTP, SFTP, TCP, UDP, IGMP, RTCP,	Dimensio
		Weight
System integra	ICMP, DHCP, ARP, SOCKS, SSH, LLDP	Included accessori
Application	Open API for software integration, including VAPIX®	
Programming Interface	and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S and ONVIF Profile G, specification at	Optional accessori
	www.onvif.org	Video
Analytics	Included	managen software
•	AXIS Video Motion Detection, active tampering alarm Supported	Language
•		
·	AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard,	
·	AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard, AXIS Perimeter Defender	Warranty
·	AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard, AXIS Perimeter Defender AXIS Digital Autotracking, AXIS People Counter, AXIS Tailgating Detector, AXIS Direction Detector,	Warranty
,	AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard, AXIS Perimeter Defender AXIS Digital Autotracking, AXIS People Counter, AXIS Tailgating Detector, AXIS Direction Detector, AXIS Occupancy Estimator, AXIS Random Inspection, AXIS Queue Monitor Support for AXIS Camera Application Platform enabling	a. This prod OpenSSI
, Event triggers	AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard, AXIS Perimeter Defender AXIS Digital Autotracking, AXIS People Counter, AXIS Tailgating Detector, AXIS Direction Detector, AXIS Occupancy Estimator, AXIS Random Inspection, AXIS Queue Monitor	a. This prod OpenSSI Young (e

	Pre- and post-alarm video or image buffering for recording or upload Notification: email, HTTP, HTTPS, TCP and SNMP trap Overlay text	
Data streaming	Event data	
Built-in installation aids	Remote zoom, remote focus, pixel counter, optimized IR with adjustable IR illumination intensity	
General		
Casing	IP52-rated, IK08 impact-resistant, polycarbonate casing with hard-coated dome and dehumidifying membrane Encapsulated electronics and captive screws Color: white NCS S 1002-B For repainting instructions of skin cover or casing and impact on warranty, contact your Axis partner.	
Sustainability	PVC free	
Memory	512 MB RAM, 256 MB Flash	
Power	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 3, max 10.2 W, typical 6.1 W	
Connectors	RJ45 10BASE-T/100BASE-TX PoE	
IR illumination	Optimized IR with power-efficient, long-life 850 nm IR LEDs with adjustable illumination intensity. Range of reach 30 m (100 ft) or more depending on scene	
Storage	Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com	
Operating conditions	0 °C to 50 °C (32 °F to 122 °F) Humidity 10 to 85% RH (non-condensing)	
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)	
Approvals	EMC EN 55022 Class B, EN 61000-6-1, EN 61000-6-2, EN 55024, EN 50121-4, IEC 62236-4, FCC Part 15 Subpart B Class A and B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24 Safety IEC/EN/UL 60950-1, IEC/EN 62471 Environment IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-14 IEC 60068-2-6 (vibration), IEC 60068-2-27 (shock), IEC 60068-2-78, IEC/EN 60529 IP52, IEC/EN 62262 IK08	
Dimensions	Height: 101 mm (4 in) ø 149 mm (5 7/8 in)	
Weight	550 g (1.2 lb)	
Included accessories	Installation Guide, Windows decoder 1-user license, mounting bracket, cable gasket, Resistorx® T20 L-key, drill template, connector guard	
Optional accessories	AXIS ACI Conduit Bracket B, AXIS ACI Conduit Adapters, AXIS T94K01L Recessed Mount Kit, AXIS T94K01D Pendant Kit, AXIS Skin Cover C, Black, AXIS Mounts, Smoked dome For more accessories, see www.axis.com	
Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/vms	
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty	

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (eay@cryptsoft.com).

Environmental responsibility:

www.axis.com/environmental-responsibility

