

POWERHOUSE MX™

TIMING PULLEYS

(Compatible with Poly Chain® GT® Carbon belts)

14 mm Pitch
For 20 mm Wide Belts
Iron
Black Oxide Plating
Taper-Lock® Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
28-14MX20-2012	28	A1F	4.912	4.802	5.562	2012	1.359	1.359
29-14MX20-2012	29	A1F	5.088	4.978	5.562	2012	1.359	1.359
30-14MX20-2012	30	A1F	5.263	5.153	5.763	2012	1.359	1.359
31-14MX20-2012	31	A1F	5.439	5.329	6.124	2012	1.359	1.359
32-14MX20-2012	32	A1F	5.614	5.504	6.124	2012	1.359	1.359
33-14MX20-2012	33	A1F	5.790	5.680	6.465	2012	1.359	1.359
34-14MX20-2012	34	A1F	5.965	5.855	6.465	2012	1.359	1.359
35-14MX20-2012	35	A1F	6.141	6.031	6.816	2012	1.359	1.359
36-14MX20-2517	36	B1F	6.316	6.206	6.816	2517	1.359	1.750
37-14MX20-2517	37	B1F	6.492	6.382	7.167	2517	1.359	1.750
38-14MX20-2517	38	B1F	6.667	6.557	7.167	2517	1.359	1.750
39-14MX20-2517	39	B1F	6.842	6.732	7.518	2517	1.359	1.750
40-14MX20-2517	40	B1F	7.018	6.908	7.518	2517	1.359	1.750
43-14MX20-2517	43	B1F	7.544	7.434	8.395	2517	1.359	1.750
45-14MX20-3020	45	B1F	7.895	7.785	8.395	3020	1.359	2.000
48-14MX20-3020	48	B1F	8.421	8.311	8.941	3020	1.359	2.000
50-14MX20-3020	50	B1F	8.772	8.662	9.292	3020	1.359	2.000
53-14MX20-3020	53	B1F	9.299	9.189	9.687	3020	1.359	2.000
56-14MX20-3525	56	B1F	9.825	9.715	10.355	3525	1.359	2.500
60-14MX20-3525	60	B1F	10.527	10.417	11.067	3525	1.359	2.500
63-14MX20-3525	63	B1F	11.053	10.943	11.750	3525	1.359	2.500
67-14MX20-3525	67	B1F	11.755	11.645	12.500	3525	1.359	2.500
71-14MX20-3525	71	C1F	12.457	12.347	13.187	3525	1.359	2.500
75-14MX20-3525	75	C1F	13.158	13.048	13.730	3525	1.359	2.500
80-14MX20-3525	80	C2F	14.036	13.926	14.625	3525	1.359	2.500
90-14MX20-3525	90	C2	15.790	15.680	-	3525	1.359	2.500
112-14MX20-3525	112	C3	19.650	19.540	-	3525	1.359	2.500
126-14MX20-3525	126	C3	22.106	21.996	-	3525	1.359	2.500
140-14MX20-3525	140	C3	24.562	24.452	-	3525	1.359	2.500
154-14MX20-3525	154	C3	27.019	26.909	-	3525	1.359	2.500
168-14MX20-3525	168	C3	29.475	29.365	-	3525	1.359	2.500
180-14MX20-3525	180	C3	31.580	31.470	-	3525	1.359	2.500
200-14MX20-3525	200	C3	35.089	34.979	-	3525	1.359	2.500
224-14MX20-4030	224	C3	39.300	39.190	-	4030	1.359	3.000

