

5 MM POWERHOUSE™ HTD® BELTS

Standard Widths:

9 mm, 15 mm, 25 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Timing Belts



Part Number	No. of Teeth	Pitch Length (mm)
790-5M	158	790.0
800-5M	160	800.0
810-5M	162	810.0
825-5M	165	825.0
830-5M	166	830.0
835-5M	167	835.0
845-5M	169	845.0
850-5M	170	850.0
860-5M	172	860.0
870-5M	174	870.0
890-5M	178	890.0
900-5M	180	900.0
920-5M	184	920.0
925-5M	185	925.0
930-5M	186	930.0
935-5M	187	935.0
940-5M	188	940.0
950-5M	190	950.0
965-5M	193	965.0
975-5M	195	975.0
980-5M	196	980.0
985-5M	197	985.0
1000-5M	200	1000.0

Part Number	No. of Teeth	Pitch Length (mm)
1025-5M	205	1025.0
1035-5M	207	1035.0
1050-5M	210	1050.0
1100-5M	220	1100.0
1115-5M	223	1115.0
1125-5M	225	1125.0
1135-5M	227	1135.0
1145-5M	229	1145.0
1175-5M	235	1175.0
1195-5M	239	1195.0
1200-5M	240	1200.0
1225-5M	245	1225.0
1235-5M	247	1235.0
1250-5M	250	1250.0
1270-5M	254	1270.0
1295-5M	259	1295.0
1350-5M	270	1350.0
1375-5M	275	1375.0
1380-5M	276	1380.0
1420-5M	284	1420.0
1425-5M	285	1425.0
1500-5M	300	1500.0
1575-5M	315	1575.0

Part Number	No. of Teeth	Pitch Length (mm)
1595-5M	319	1595.0
1635-5M	327	1635.0
1690-5M	338	1690.0
1720-5M	344	1720.0
1790-5M	358	1790.0
1800-5M	360	1800.0
1870-5M	374	1870.0
1895-5M	379	1895.0
1945-5M	389	1945.0
1980-5M	396	1980.0
2000-5M	400	2000.0
2100-5M	420	2100.0
2110-5M	422	2110.0
2250-5M	450	2250.0
2350-5M	470	2350.0
2525-5M	505	2525.0
2760-5M	552	2760.0
3120-5M	624	3120.0
3170-5M	634	3170.0
3430-5M	686	3430.0
3800-5M	760	3800.0

Neoprene 5 mm POWERHOUSE™ HTD® timing belt part numbers can be determined as follows:
Pitch Length Code + -5M- + Width Code