

# 3 MM POWERHOUSE™ HTD® BELTS

Standard Widths:

6 mm, 9 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Timing Belts



Part Number	No. of Teeth	Pitch Length (mm)
87-3M	29	87.0
102-3M	34	102.0
105-3M	35	105.0
108-3M	36	108.0
111-3M	37	111.0
117-3M	39	117.0
120-3M	40	120.0
123-3M	41	123.0
126-3M	42	126.0
129-3M	43	129.0
132-3M	44	132.0
141-3M	47	141.0
144-3M	48	144.0
147-3M	49	147.0
150-3M	50	150.0
153-3M	51	153.0
156-3M	52	156.0
159-3M	53	159.0
165-3M	55	165.0
168-3M	56	168.0
171-3M	57	171.0
174-3M	58	174.0
177-3M	59	177.0
180-3M	60	180.0
183-3M	61	183.0
186-3M	62	186.0
189-3M	63	189.0
192-3M	64	192.0
195-3M	65	195.0
198-3M	66	198.0
201-3M	67	201.0

Part Number	No. of Teeth	Pitch Length (mm)
204-3M	68	204.0
207-3M	69	207.0
210-3M	70	210.0
213-3M	71	213.0
216-3M	72	216.0
219-3M	73	219.0
222-3M	74	222.0
225-3M	75	225.0
228-3M	76	228.0
234-3M	78	234.0
237-3M	79	237.0
240-3M	80	240.0
246-3M	82	246.0
249-3M	83	249.0
252-3M	84	252.0
255-3M	85	255.0
258-3M	86	258.0
261-3M	87	261.0
264-3M	88	264.0
267-3M	89	267.0
270-3M	90	270.0
276-3M	92	276.0
279-3M	93	279.0
282-3M	94	282.0
285-3M	95	285.0
288-3M	96	288.0
291-3M	97	291.0
294-3M	98	294.0
297-3M	99	297.0
300-3M	100	300.0
303-3M	101	303.0

Part Number	No. of Teeth	Pitch Length (mm)
306-3M	102	306.0
309-3M	103	309.0
312-3M	104	312.0
315-3M	105	315.0
318-3M	106	318.0
324-3M	108	324.0
327-3M	109	327.0
330-3M	110	330.0
333-3M	111	333.0
336-3M	112	336.0
339-3M	113	339.0
342-3M	114	342.0
345-3M	115	345.0
351-3M	117	351.0
357-3M	119	357.0
360-3M	120	360.0
363-3M	121	363.0
366-3M	122	366.0
369-3M	123	369.0
372-3M	124	372.0
375-3M	125	375.0
381-3M	127	381.0
384-3M	128	384.0
387-3M	129	387.0
390-3M	130	390.0
393-3M	131	393.0
396-3M	132	396.0
399-3M	133	399.0
402-3M	134	402.0
405-3M	135	405.0
411-3M	137	411.0

Neoprene 3 mm POWERHOUSE™ HTD® timing belt part numbers can be determined as follows:  
Pitch Length Code + -3M- + Width Code