

# POWERHOUSE™ TIMING PULLEYS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

**14 mm Pitch**  
**For 40 mm Wide Belts**  
**Iron**  
**Black Oxide Plating**  
**Taper-Lock® Style**



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
28-14P40-2012	28	A1F	4.912	4.802	5.562	2012	2.130	2.130
29-14P40-2012	29	A1F	5.088	4.978	5.562	2012	2.130	2.130
30-14P40-2012	30	A1F	5.263	5.153	5.763	2012	2.130	2.130
31-14P40-2012	31	A1F	5.439	5.329	6.124	2012	2.130	2.130
32-14P40-2012	32	A1F	5.614	5.504	6.124	2012	2.130	2.130
33-14P40-2012	33	A1F	5.790	5.680	6.465	2012	2.130	2.130
34-14P40-2012	34	A1F	5.965	5.855	6.465	2012	2.130	2.130
35-14P40-2012	35	A1F	6.141	6.031	6.816	2012	2.130	2.130
36-14P40-2517	36	A1F	6.316	6.206	6.816	2517	2.130	2.130
37-14P40-2517	37	A1F	6.492	6.382	7.167	2517	2.130	2.130
38-14P40-2517	38	A1F	6.669	6.559	7.167	2517	2.130	2.130
39-14P40-2517	39	A1F	6.842	6.732	7.518	2517	2.130	2.130
40-14P40-2517	40	A1F	7.018	6.908	7.518	2517	2.130	2.130
42-14P40-2517	42	A1F	7.369	7.259	8.044	2517	2.130	2.130
44-14P40-2517	44	A1F	7.720	7.610	8.395	2517	2.130	2.130
46-14P40-2517	46	A1F	8.070	7.960	8.395	2517	2.130	2.130
48-14P40-2517	48	A1F	8.421	8.311	8.941	2517	2.130	2.130
50-14P40-2517	50	A1F	8.772	8.662	9.292	2517	2.130	2.130
52-14P40-2517	52	A1F	9.123	9.013	9.687	2517	2.130	2.130
56-14P40-2517	56	A1F	9.825	9.715	10.355	2517	2.130	2.130
60-14P40-3020	60	A1F	10.527	10.417	11.067	3020	2.130	2.130
64-14P40-3020	64	A1F	11.229	11.119	11.750	3020	2.130	2.130
68-14P40-3020	68	D1F	11.930	11.820	12.500	3020	2.130	2.130
72-14P40-3020	72	D1F	12.632	12.522	13.187	3020	2.130	2.130
80-14P40-3020	80	D3F	14.036	13.926	14.625	3020	2.130	2.130
90-14P40-3020	90	D3	15.790	15.680	-	3020	2.130	2.130
112-14P40-3020	112	A3	19.650	19.540	-	3020	2.130	2.130
144-14P40-3020	144	A3	25.264	25.154	-	3020	2.130	2.130
168-14P40-3020	168	A3	29.475	29.365	-	3020	2.130	2.130
192-14P40-3020	192	A3	33.686	33.576	-	3020	2.130	2.130

