

IDLER PULLEYS

Needle Bearing

Steel/Iron

Black Oxide Plating



Part Number	No. of Teeth	Diametral Pitch	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore (in)	Face Width (in)	Overall Length (in)
22XL075-IDLER	22	XL (0.200")	1.401	1.381	1.625	0.500	0.750	0.750
24XL050-IDLER	24	XL (0.200")	1.528	1.508	1.750	0.500	0.500	0.500
18L100-IDLER	18	L (0.375")	2.149	2.119	2.375	1.000	1.000	1.000
22L100-IDLER	22	L (0.375")	2.626	2.602	-	1.000	1.000	1.000
16H100-IDLER	16	H (0.500")	2.546	2.499	-	1.000	1.000	1.000
16H200-IDLER	16	H (0.500")	2.546	2.499	-	1.000	2.000	2.000
18H300-IDLER	18	H (0.500")	2.546	2.499	3.100	1.000	3.000	3.000
18XH200-IDLER	18	XH (0.875")	5.013	4.903	5.556	1.000	2.000	2.000
18XH300-IDLER	18	XH (0.875")	5.013	4.903	5.556	1.000	3.000	3.000
19-8M50-IDLER	19	8 mm POWERHOUSE™ HTD®	1.905	1.851	-	1.000	1.313	1.313
29-8M30-IDLER	29	8 mm POWERHOUSE™ HTD®	2.907	2.859	-	1.000	2.063	2.063
29-8M85-IDLER	29	8 mm POWERHOUSE™ HTD®	2.907	2.859	-	1.000	3.438	3.438
27-14M40-IDLER	27	14 mm POWERHOUSE™ HTD®	4.737	4.627	-	1.000	1.625	1.625
27-14M55-IDLER	27	14 mm POWERHOUSE™ HTD®	4.737	4.627	-	1.000	2.313	2.313
27-14M85-IDLER	27	14 mm POWERHOUSE™ HTD®	4.737	4.627	-	1.000	3.500	3.500
31-14M115-IDLER	31	14 mm POWERHOUSE™ HTD®	5.439	5.333	6.124	1.500	4.750	4.750
32-8P20-IDLER	32	8 mm POWERHOUSE™	3.208	3.154	3.543	1.250	1.240	1.800
36-8P30-IDLER	36	8 mm POWERHOUSE™	3.609	3.555	3.938	1.910	1.860	1.860
30-14P40-IDLER	30	14 mm POWERHOUSE™	5.263	5.153	5.760	2.550	2.060	2.310
34-14P55-IDLER	34	14 mm POWERHOUSE™	5.965	5.855	6.465	3.380	3.330	4.330
32-8MX12-IDLER	32	8 mm POWERHOUSE MX™	3.208	3.145	3.543	1.250	0.850	1.790
32-8MX21-IDLER	32	8 mm POWERHOUSE MX™	3.208	3.145	3.543	1.250	1.240	1.800
36-8MX36-IDLER	36	8 mm POWERHOUSE MX™	3.609	3.546	3.938	1.910	1.860	1.860
36-8MX62-IDLER	36	8 mm POWERHOUSE MX™	3.609	3.546	3.938	1.910	2.910	3.600
30-14MX20-IDLER	30	14 mm POWERHOUSE MX™	5.263	5.153	5.760	2.550	1.360	2.360
30-14MX37-IDLER	30	14 mm POWERHOUSE MX™	5.263	5.153	5.760	2.550	2.060	2.310
34-14MX68-IDLER	34	14 mm POWERHOUSE MX™	5.965	5.855	6.465	3.380	3.330	4.330
34-14MX90-IDLER	34	14 mm POWERHOUSE MX™	5.965	5.855	6.465	3.380	4.200	5.200
34-14MX125-IDLER	34	14 mm POWERHOUSE MX™	5.965	5.855	6.465	3.380	5.630	6.720