


XL TIMING PULLEY BAR STOCK

0.200" / 5.08 mm Pitch

Steel



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
10XL-PS6S	10	16.2 mm	15.7 mm	0.637"	0.617"	0.500"	0.875"	6.000"	6.875"
11XL-PS6S	11	17.8 mm	17.3 mm	0.700"	0.680"	0.500"	0.875"	6.000"	6.875"
12XL-PS8S	12	19.4 mm	18.9 mm	0.764"	0.744"	0.500"	0.750"	8.000"	8.750"
13XL-PS8S	13	21.0 mm	20.5 mm	0.828"	0.808"	0.500"	0.750"	8.000"	8.750"
14XL-PS8S	14	22.6 mm	22.1 mm	0.891"	0.871"	0.500"	0.750"	8.000"	8.750"
15XL-PS8S	15	24.3 mm	23.7 mm	0.955"	0.935"	0.500"	0.750"	8.000"	8.750"
16XL-PS8S	16	25.9 mm	25.4 mm	1.019"	0.999"	0.500"	0.750"	8.000"	8.750"
17XL-PS8S	17	27.5 mm	27.0 mm	1.082"	1.062"	0.500"	0.750"	8.000"	8.750"
18XL-PS8S	18	29.1 mm	28.6 mm	1.146"	1.126"	0.500"	0.750"	8.000"	8.750"
19XL-PS8S	19	30.7 mm	30.2 mm	1.210"	1.190"	0.500"	0.750"	8.000"	8.750"
20XL-PS8S	20	32.3 mm	31.8 mm	1.273"	1.253"	0.500"	0.750"	8.000"	8.750"
21XL-PS8S	21	34.0 mm	33.5 mm	1.337"	1.317"	0.500"	0.750"	8.000"	8.750"
22XL-PS8S	22	35.6 mm	35.1 mm	1.401"	1.381"	0.500"	0.750"	8.000"	8.750"
23XL-PS8S	23	37.2 mm	36.7 mm	1.464"	1.444"	0.500"	0.750"	8.000"	8.750"
24XL-PS8S	24	38.8 mm	38.3 mm	1.528"	1.508"	0.500"	0.750"	8.000"	8.750"
25XL-PS8S	25	40.4 mm	39.9 mm	1.592"	1.572"	0.500"	0.750"	8.000"	8.750"
26XL-PS8S	26	42.0 mm	41.5 mm	1.655"	1.635"	0.500"	0.750"	8.000"	8.750"
27XL-PS8S	27	43.7 mm	43.2 mm	1.719"	1.699"	0.500"	0.750"	8.000"	8.750"
28XL-PS8S	28	45.3 mm	44.8 mm	1.783"	1.763"	0.500"	0.750"	8.000"	8.750"
29XL-PS8S	29	46.9 mm	46.4 mm	1.846"	1.826"	0.500"	0.750"	8.000"	8.750"
30XL-PS8S	30	48.5 mm	48.0 mm	1.910"	1.890"	0.500"	0.750"	8.000"	8.750"
31XL-PS8S	31	50.1 mm	49.6 mm	1.974"	1.954"	0.500"	0.750"	8.000"	8.750"
32XL-PS8S	32	51.7 mm	51.2 mm	2.037"	2.017"	0.500"	0.750"	8.000"	8.750"
33XL-PS8S	33	53.4 mm	52.9 mm	2.101"	2.081"	0.500"	1.000"	8.000"	9.000"
34XL-PS8S	34	55.0 mm	54.5 mm	2.165"	2.145"	0.500"	1.000"	8.000"	9.000"