


# AT10 TIMING PULLEY BAR STOCK

AT10 mm Pitch  
Aluminum

METRIC TIMING PULLEY STOCK



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
15AT10-PS160A	15	47.7 mm	45.9 mm	1.878"	1.807"	0.500"	0.800"	6.300"	7.100"
16AT10-PS160A	16	50.9 mm	49.0 mm	2.004"	1.931"	0.500"	0.800"	6.300"	7.100"
17AT10-PS160A	17	54.1 mm	52.2 mm	2.130"	2.057"	0.500"	0.800"	6.300"	7.100"
18AT10-PS160A	18	57.2 mm	55.4 mm	2.252"	2.183"	0.750"	1.000"	6.300"	7.300"
19AT10-PS160A	19	60.4 mm	58.6 mm	2.378"	2.307"	0.750"	1.000"	6.300"	7.300"
20AT10-PS160A	20	63.6 mm	61.8 mm	2.504"	2.433"	0.750"	1.000"	6.300"	7.300"
21AT10-PS160A	21	66.8 mm	65.0 mm	2.630"	2.559"	0.750"	1.000"	6.300"	7.300"
22AT10-PS160A	22	70.0 mm	68.1 mm	2.756"	2.683"	0.750"	1.000"	6.300"	7.300"
23AT10-PS160A	23	73.2 mm	71.3 mm	2.882"	2.809"	0.750"	1.000"	6.300"	7.300"
24AT10-PS160A	24	76.3 mm	74.5 mm	3.004"	2.935"	0.750"	1.000"	6.300"	7.300"
25AT10-PS160A	25	79.5 mm	77.7 mm	3.130"	3.059"	0.750"	1.000"	6.300"	7.300"
26AT10-PS160A	26	82.7 mm	80.9 mm	3.256"	3.185"	0.750"	1.000"	6.300"	7.300"
27AT10-PS160A	27	85.9 mm	84.1 mm	3.382"	3.311"	0.750"	1.000"	6.300"	7.300"
28AT10-PS160A	28	89.1 mm	87.2 mm	3.508"	3.435"	0.750"	1.000"	6.300"	7.300"
29AT10-PS160A	29	92.3 mm	90.4 mm	3.634"	3.561"	0.750"	1.000"	6.300"	7.300"
30AT10-PS160A	30	95.4 mm	93.6 mm	3.756"	3.687"	0.750"	1.000"	6.300"	7.300"
31AT10-PS160A	31	98.6 mm	96.8 mm	3.882"	3.811"	0.750"	1.000"	6.300"	7.300"
32AT10-PS160A	32	101.8 mm	100.0 mm	4.008"	3.937"	0.750"	1.000"	6.300"	7.300"
33AT10-PS160A	33	105.0 mm	103.2 mm	4.134"	4.063"	1.000"	1.000"	6.300"	7.300"
34AT10-PS160A	34	108.2 mm	106.4 mm	4.260"	4.189"	1.000"	1.000"	6.300"	7.300"
35AT10-PS106A	35	111.3 mm	109.6 mm	4.382"	4.313"	1.000"	1.000"	6.300"	7.300"
36AT10-PS160A	36	114.5 mm	112.8 mm	4.508"	4.439"	1.000"	1.000"	6.300"	7.300"
37AT10-PS160A	37	117.7 mm	115.9 mm	4.634"	4.563"	1.000"	1.000"	6.300"	7.300"