


5 MM POWERHOUSE™ TIMING PULLEY BAR STOCK

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

5 mm Pitch Aluminum



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
35-5P-PS8A	35	55.7 mm	54.6 mm	2.193"	2.148"	0.750"	1.000"	8.000"	9.000"
36-5P-PS8A	36	57.3 mm	56.2 mm	2.256"	2.211"	0.750"	1.000"	8.000"	9.000"
38-5P-PS8A	38	60.5 mm	59.3 mm	2.381"	2.336"	0.750"	1.000"	8.000"	9.000"
40-5P-PS8A	40	63.7 mm	62.5 mm	2.506"	2.461"	0.750"	1.000"	8.000"	9.000"
42-5P-PS8A	42	66.9 mm	65.7 mm	2.632"	2.587"	0.750"	1.000"	8.000"	9.000"
44-5P-PS8A	44	70.0 mm	68.9 mm	2.757"	2.712"	0.750"	1.000"	8.000"	9.000"
45-5P-PS8A	45	71.6 mm	70.5 mm	2.820"	2.775"	0.750"	1.000"	8.000"	9.000"
46-5P-PS8A	46	73.2 mm	72.1 mm	2.882"	2.837"	0.750"	1.000"	8.000"	9.000"
48-5P-PS8A	48	76.4 mm	75.3 mm	3.008"	2.963"	0.750"	1.000"	8.000"	9.000"
50-5P-PS8A	50	79.6 mm	78.4 mm	3.133"	3.088"	0.750"	1.000"	8.000"	9.000"
54-5P-PS8A	54	86.0 mm	84.8 mm	3.384"	3.339"	0.750"	1.000"	8.000"	9.000"
56-5P-PS8A	56	89.1 mm	88.0 mm	3.509"	3.464"	0.750"	1.000"	8.000"	9.000"
60-5P-PS8A	60	95.5 mm	94.4 mm	3.760"	3.715"	0.750"	1.000"	8.000"	9.000"
62-5P-PS8A	62	98.7 mm	97.5 mm	3.885"	3.840"	0.750"	1.000"	8.000"	9.000"
65-5P-PS8A	65	103.5 mm	102.3 mm	4.073"	4.028"	0.750"	1.000"	8.000"	9.000"
72-5P-PS8A	72	114.6 mm	113.4 mm	4.511"	4.466"	1.000"	1.000"	8.000"	9.000"
80-5P-PS8A	80	127.3 mm	126.2 mm	5.013"	4.968"	1.000"	1.000"	8.000"	9.000"
90-5P-PS8A	90	143.2 mm	142.1 mm	5.639"	5.594"	1.000"	1.000"	8.000"	9.000"
100-5P-PS8A	100	159.2 mm	158.0 mm	6.266"	6.221"	1.000"	1.000"	8.000"	9.000"
112-5P-PS8A	112	178.3 mm	177.1 mm	7.018"	6.973"	1.000"	1.000"	8.000"	9.000"
126-5P-PS8A	126	200.5 mm	199.4 mm	7.895"	7.850"	1.000"	1.000"	8.000"	9.000"