

3 MM POWERHOUSE™ HTD® BELTS

Standard Widths:

6 mm, 9 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Part Number	No. of Teeth	Pitch Length (mm)
417-3M	139	417.0
420-3M	140	420.0
423-3M	141	423.0
426-3M	142	426.0
432-3M	144	432.0
435-3M	145	435.0
438-3M	146	438.0
444-3M	148	444.0
447-3M	149	447.0
459-3M	153	459.0
462-3M	154	462.0
465-3M	155	465.0
468-3M	156	468.0
471-3M	157	471.0
474-3M	158	474.0
477-3M	159	477.0
480-3M	160	480.0
483-3M	161	483.0
486-3M	162	486.0
489-3M	163	489.0
492-3M	164	492.0
495-3M	165	495.0
501-3M	167	501.0
504-3M	168	504.0
510-3M	170	510.0
513-3M	171	513.0
516-3M	172	516.0
519-3M	173	519.0
522-3M	174	522.0
525-3M	175	525.0
528-3M	176	528.0

Part Number	No. of Teeth	Pitch Length (mm)
531-3M	177	531.0
537-3M	179	537.0
549-3M	183	549.0
552-3M	184	552.0
558-3M	186	558.0
564-3M	188	564.0
570-3M	190	570.0
573-3M	191	573.0
576-3M	192	576.0
579-3M	193	579.0
582-3M	194	582.0
585-3M	195	585.0
591-3M	197	591.0
594-3M	198	594.0
597-3M	199	597.0
600-3M	200	600.0
606-3M	202	606.0
609-3M	203	609.0
612-3M	204	612.0
615-3M	205	615.0
627-3M	209	627.0
633-3M	211	633.0
639-3M	213	639.0
645-3M	215	645.0
648-3M	216	648.0
654-3M	218	654.0
657-3M	219	657.0
663-3M	221	663.0
669-3M	223	669.0
672-3M	224	672.0
675-3M	225	675.0

Part Number	No. of Teeth	Pitch Length (mm)
681-3M	227	681.0
684-3M	228	684.0
687-3M	229	687.0
690-3M	230	690.0
693-3M	231	693.0
696-3M	232	696.0
702-3M	234	702.0
705-3M	235	705.0
708-3M	236	708.0
711-3M	237	711.0
720-3M	240	720.0
723-3M	241	723.0
732-3M	244	732.0
735-3M	245	735.0
738-3M	246	738.0
750-3M	250	750.0
753-3M	251	753.0
783-3M	261	783.0
795-3M	265	795.0
804-3M	268	804.0
816-3M	272	816.0
822-3M	274	822.0
825-3M	275	825.0
837-3M	279	837.0
843-3M	281	843.0
858-3M	286	858.0
861-3M	287	861.0
873-3M	291	873.0
882-3M	294	882.0
888-3M	296	888.0
891-3M	297	891.0

Neoprene 3 mm POWERHOUSE™ HTD® timing belt part numbers can be determined as follows:
Pitch Length Code + -3M- + Width Code