

5 MM POWERHOUSE™ HTD® BELTS

Standard Widths:

9 mm, 15 mm, 25 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Part Number	No. of Teeth	Pitch Length (mm)
175-5M	35	175.0
180-5M	36	180.0
200-5M	40	200.0
215-5M	43	215.0
225-5M	45	225.0
230-5M	46	230.0
240-5M	48	240.0
245-5M	49	245.0
255-5M	51	255.0
260-5M	52	260.0
265-5M	53	265.0
270-5M	54	270.0
275-5M	55	275.0
280-5M	56	280.0
285-5M	57	285.0
295-5M	59	295.0
300-5M	60	300.0
305-5M	61	305.0
310-5M	62	310.0
320-5M	64	320.0
325-5M	65	325.0
330-5M	66	330.0
335-5M	67	335.0
340-5M	68	340.0
345-5M	69	345.0
350-5M	70	350.0
360-5M	72	360.0

Part Number	No. of Teeth	Pitch Length (mm)
365-5M	73	365.0
370-5M	74	370.0
375-5M	75	375.0
385-5M	77	385.0
400-5M	80	400.0
405-5M	81	405.0
410-5M	82	410.0
415-5M	83	415.0
420-5M	84	420.0
425-5M	85	425.0
450-5M	90	450.0
460-5M	92	460.0
465-5M	93	465.0
475-5M	95	475.0
480-5M	96	480.0
495-5M	99	495.0
500-5M	100	500.0
520-5M	104	520.0
525-5M	105	525.0
535-5M	107	535.0
540-5M	108	540.0
550-5M	110	550.0
555-5M	111	555.0
560-5M	112	560.0
565-5M	113	565.0
575-5M	115	575.0
580-5M	116	580.0

Part Number	No. of Teeth	Pitch Length (mm)
585-5M	117	585.0
590-5M	118	590.0
600-5M	120	600.0
610-5M	122	610.0
615-5M	123	615.0
620-5M	124	620.0
625-5M	125	625.0
630-5M	126	630.0
635-5M	127	635.0
640-5M	128	640.0
645-5M	129	645.0
655-5M	131	655.0
665-5M	133	665.0
670-5M	134	670.0
680-5M	136	680.0
685-5M	137	685.0
695-5M	139	695.0
700-5M	140	700.0
710-5M	142	710.0
720-5M	144	720.0
740-5M	148	740.0
745-5M	149	745.0
750-5M	150	750.0
755-5M	151	755.0
765-5M	153	765.0
770-5M	154	770.0
775-5M	155	775.0

Neoprene 5 mm POWERHOUSE™ HTD® timing belt part numbers can be determined as follows:
Pitch Length Code + -5M- + Width Code