

# POWERHOUSE MX™

## TIMING PULLEYS

(Compatible with Poly Chain® GT® Carbon belts)

14 mm Pitch

For 37 mm Wide Belts

Flanges

Iron

Black Oxide Plating



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore/Bushing	Face Width (in)	Overall Length (in)
28-14MX37-6FS10	28	6F	4.912	4.802	5.562	1.000	2.063	2.859
28-14MX37-2012	28	A1F	4.912	4.802	5.562	2012	1.690	2.000
29-14MX37-2517	29	A1F	5.088	4.978	5.562	2517	1.690	2.000
30-14MX37-2517	30	A1F	5.263	5.153	5.763	2517	1.690	2.000
31-14MX37-2517	31	A1F	5.439	5.329	6.124	2517	1.690	2.000
32-14MX37-2517	32	A1F	5.614	5.504	6.124	2517	1.690	2.000
33-14MX37-2517	33	A1F	5.790	5.680	6.465	2517	1.690	2.000
34-14MX37-2517	34	A1F	5.965	5.855	6.465	2517	1.690	2.000
35-14MX37-2517	35	A1F	6.141	6.031	6.816	2517	1.690	2.000
36-14MX37-2517	36	A1F	6.316	6.206	6.816	2517	1.690	2.000
37-14MX37-2517	37	A1F	6.492	6.382	7.167	2517	1.690	2.000
38-14MX37-3020	38	A1F	6.667	6.557	7.167	3020	1.750	2.063
39-14MX37-3020	39	A1F	6.842	6.732	7.518	3020	1.750	2.063
40-14MX37-3020	40	A1F	7.018	6.908	7.518	3020	1.750	2.063
43-14MX37-3020	43	A1F	7.544	7.434	8.395	3020	1.750	2.063
45-14MX37-3020	45	A1F	7.895	7.785	8.395	3020	1.750	2.063
48-14MX37-3020	48	A1F	8.421	8.311	8.941	3020	1.750	2.063
50-14MX37-3020	50	A1F	8.772	8.662	9.292	3020	1.750	2.063
53-14MX37-3020	53	A1F	9.299	9.189	9.687	3020	1.750	2.063
56-14MX37-3525	56	B1F	9.825	9.715	10.355	3525	2.063	2.500
60-14MX37-3525	60	B1F	10.527	10.417	11.067	3525	2.063	2.500
63-14MX37-3525	63	B1F	11.053	10.943	11.750	3525	2.063	2.500
67-14MX37-3525	67	B1F	11.755	11.645	12.500	3525	2.063	2.500
71-14MX37-3525	71	B1F	12.457	12.347	13.187	3525	2.063	2.500
75-14MX37-3525	75	C1F	13.158	13.048	13.730	3525	2.063	2.500
80-14MX37-3525	80	C2F	14.036	13.926	14.625	3525	2.063	2.500

