

POWERHOUSE MX™

TIMING PULLEYS

(Compatible with Poly Chain® GT® Carbon belts)

14 mm Pitch

For 125 mm Wide Belts

Iron

Black Oxide Plating



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore/ Bushing	Face Width (in)	Overall Length (in)
28-14MX125-6FS16	28	6F	4.912	4.802	5.562	1.500	5.609	6.500
29-14MX125-6FS16	29	6F	5.088	4.978	5.562	1.500	5.609	6.500
30-14MX125-6FS16	30	6F	5.263	5.153	5.763	1.500	5.609	6.500
31-14MX125-6FS16	31	6F	5.439	5.329	6.124	1.500	5.609	6.500
32-14MX125-6FS16	32	6F	5.614	5.504	6.124	1.500	5.609	6.500
33-14MX125-6FS16	33	6F	5.790	5.680	6.465	1.500	5.609	6.688
34-14MX125-6FS16	34	6F	5.965	5.855	6.465	1.500	5.609	6.688
35-14MX125-6FS16	35	6F	6.141	6.031	6.816	1.500	5.609	6.688
36-14MX125-6FS16	36	6F	6.316	6.206	6.816	1.500	5.609	6.688
37-14MX125-6FS16	37	6F	6.492	6.382	7.167	1.500	5.609	6.688
38-14MX125-6FS16	38	6F	6.667	6.557	7.167	1.500	5.609	6.688
39-14MX125-6FS16	39	6F	6.842	6.732	7.518	1.500	5.609	6.688
40-14MX125-6FS16	40	6F	7.018	6.908	7.518	1.500	5.609	6.688
43-14MX125-6FS16	43	6F	7.544	7.434	8.395	1.500	5.609	6.813
45-14MX125-6FS16	45	6F	7.895	7.785	8.395	1.500	5.609	6.813
48-14MX125-6FS16	48	6F	8.421	8.311	8.941	1.500	5.609	6.813
50-14MX125-4535	50	A1F	8.772	8.662	9.292	4535	5.609	5.609
53-14MX125-4535	53	A1F	9.299	9.189	9.687	4535	5.609	5.609
56-14MX125-4535	56	A1F	9.825	9.715	10.355	4535	5.609	5.609
60-14MX125-4535	60	A1F	10.527	10.417	11.067	4535	5.609	5.609
63-14MX125-4535	63	A1F	11.053	10.943	11.750	4535	5.609	5.609
67-14MX125-4535	67	A1F	11.755	11.645	12.500	4535	5.609	5.609
71-14MX125-5040	71	A1F	12.457	12.347	13.187	5040	5.609	5.609
75-14MX125-5040	75	A1F	13.158	13.048	13.730	5040	5.609	5.609
80-14MX125-5040	80	A1F	14.036	13.926	14.625	5040	5.609	5.609
90-14MX125-5040	90	D1	15.790	15.680	-	5040	5.609	5.609
112-14MX125-6050	112	A1	19.650	19.540	-	6050	5.609	5.609
140-14MX125-6050	140	D3	24.562	24.452	-	6050	5.609	5.609
168-14MX125-7060	168	C3	29.475	29.365	-	7060	5.609	5.609
180-14MX125-7060	180	C3	31.580	31.470	-	7060	5.609	5.609
200-14MX125-7060	200	C3	35.089	34.979	-	7060	5.609	5.609
224-14MX125-7060	224	C3	39.300	39.190	-	7060	5.609	5.609

