

POWERHOUSE™ HTD®

TIMING PULLEYS

14 mm Pitch

For 55 mm Wide Belts

Iron

Black Oxide Plating

QD® Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore / Bushing	Face Width (in)	Overall Length (in)
QD28-14M-55	28	E1F	4.912	4.802	5.560	SK	2.750	2.750
QD29-14M-55	29	E1F	5.088	4.978	5.560	SK	2.750	2.750
QD30-14M-55	30	A1F	5.263	5.153	6.130	SK	2.750	2.750
QD32-14M-55	32	A1F	5.614	5.504	6.130	SK	2.750	2.750
QD34-14M-55	34	A1F	5.965	5.855	6.500	SK	2.750	2.750
QD36-14M-55	36	A1F	6.316	6.206	6.810	SF	2.750	2.750
QD38-14M-55	38	A1F	6.667	6.557	7.160	SF	2.750	2.750
QD40-14M-55	40	A1F	7.018	6.909	7.500	SF	2.750	2.750
QD44-14M-55	44	D1F	7.720	7.610	8.220	E	2.750	2.750
QD48-14M-55	48	D1F	8.421	8.311	8.940	E	2.750	2.750
QD52-14M-55	52	D1F	9.123	9.013	9.690	E	2.750	2.750
QD56-14M-55	56	D1F	9.825	9.715	10.380	E	2.750	2.750
QD60-14M-55	60	D1F	10.527	10.417	11.060	E	2.750	2.750
QD64-14M-55	64	C1F	11.229	11.119	11.750	F	2.750	2.750
QD68-14M-55	68	D2F	11.930	11.820	12.500	F	2.750	2.750
QD72-14M-55	72	C2F	12.632	12.522	13.190	F	2.750	2.750
QD80-14M-55	80	C2F	14.036	13.925	14.630	F	2.750	2.750
QD90-14M-55	90	D3	15.790	15.680	-	F	2.750	2.750
QD112-14M-55	112	D3	19.650	19.540	-	F	2.750	2.750
QD144-14M-55	144	D3	25.264	25.154	-	F	2.750	2.750
QD168-14M-55	168	D3	29.475	29.365	-	F	2.750	2.750
QD192-14M-55	192	D3	33.686	33.576	-	F	2.750	2.750
QD216-14M-55	216	D3	37.896	37.786	-	F	2.750	2.750

