3078 series | post & wall

location: WET

SPECIFICATIONS:

DESCRIPTION

Outdoor post-mount or wall mount lantern features handcrafted European glass.

LAMPING

Standard: 75W A19 120V, lamps not included. **CFL**: 18W CFL 120V, lamps not included.

GU24 CFL: Self-ballasted GU24 lampholders. 18W max, 120V, lamps not

included.

DIFFUSER

Glass diffuser is hand-painted in various decors with Opal Glossy glass. The Black and Bronze finishes are opaque, while the White is semi-translucent for increased light output.

Dimensions are 8.75" Dia. x 8.5" H.

CONSTRUCTION


Post fitter or wall bracket cast aluminum with powder coated finish.


MOUNTING

Post fitter is suitable for installation onto a 3" post (not included). Wall bracket installs directly to a 4" octagonal outlet box, centered on fixture. 75°C supply wire required for incandescent lamping.

LABELS

UL or ETL Listed. Suitable for Wet Locations. May be used in Interior or Exterior applications.





All dimensions provided are nominal.
Allowance must be made for dimensional tolerance in handcrafted glasses.



ORDERING:

GU24 1x GU24, 18W max

Bronze/Opal

REV 7/13