

Heavy Duty No-Hub Couplings



DESCRIPTION

Black Swan's Heavy Duty No-Hub Couplings are high quality no-hub couplings. Gasket is made of 100% neoprene and complies with ASTM C 564. Uses FOUR TO SIX clamps depending on size of coupling. Clamps are made of stainless steel. Works extremely well in all temperatures. UPC Approved. Made in China.

Ideal for underground or above ground use.

For best results, use **Black Swan's No-Hub Sealant** when making installation.

DIRECTIONS

1. Clean pipe of dirt and debris.
2. Apply liberal coat of **Black Swan's No-Hub Sealant** to pipe.
3. Place gasket on end of one pipe and push pipe in firmly.
4. Place second pipe into gasket and pack in firmly.
5. Make sure both pipes are aligned properly.
6. Slide clamp over the gasket so the gasket is completely covered.
7. Use a calibrated torque wrench and tighten the stainless steel screws alternatively to the proper torque pounds (60 inch pounds).

UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
21300	1-1/2"	0 54647 21300 2	1.051
21310	2"	0 54647 21310 1	1.554
21320	3"	0 54647 21320 0	1.840
21330	4"	0 54647 21330 9	2.583
21340	5"	0 54647 21340 8	1.775
21350	6"	0 54647 21350 7	2.474
21360	8"	0 54647 21360 6	3.619
21370	10"	0 54647 21370 5	3.704