

Miller DuraFlex® Ultra Series Stretchable Harnesses

Materials

Webbing (DuraFlex).....Polyester, Urethane Elastomer
Webbing1-3/4" Dacron polyester
Minimum Tensile.....5000 lbs. on webbing
Thread:.....6 cord bonded 3 strand polyester thread. Minimum tensile of 42 lbs.

Grommets.....Brass
Hardware.....Steel Minimum Tensile strength
D-Rings.....5000 lbs. (22kN)
Buckles.....4000 lbs. (18kN)

* All hardware meets ASTM (50) fifty-hour salt spray test requirements.

Technical

Max Working Load:.....400 lbs - 181.4 kg

Identification

Label Materials.....Lexan and Valeron

Certification

Meets OSHA 1926.502; ANSI A10.14, Z359.1 and CSA Z259.10-M90.

Harness Description Keys

Webbing

D = DuraFlex Stretchable Webbing
 P = Polyester Webbing

D-Rings

B = Sliding Back D-Ring
 FD = Front D-Ring
 F = Front O-Ring
 H = Shoulder D-Rings
 S = Side Positioning D-Rings
 W = Sliding Back web D-Ring
 X = D-Ring Web Extension

Special Features

AB = Attached Waist Belt
 AL = Adjustable Belt Loops
 BL = Belt Loops
 BP = Back Pad
 BDP = Back D-ring Pad
 HP = Shoulder Pads
 LP = Leg Pads
 LR = Lanyard Ring
 RB = Removable Waist Belt
 SP = Sub-Pelvic Strap
 SR = Self Rescue Loops
 SS = Saddle Seat
 TO = Tool Belt Buckles

Shoulder/Leg Buckles

FB = Friction Buckles
 MB = Mating Buckles
 TB = Tongue Buckles

Quick Connect Buckles



Back D-ring Pad



E650QC
Shown in Green



E650-7QC
Shown in Green



E650-77QC
Shown in Green

Also available in blue polyester webbing for greater chemical resistance. (Model E650DQC)



| Model No. | Web Type | D-Rings | Shoulder Straps | Leg Straps | Chest Strap | Special Features | Weight |
|-------------------|----------|---------|-----------------|------------|-------------|--------------------|--------------------|
| E650QC | D | B | FB | QC | QC | SP, LR,BDP | 3.45 lbs. (1.6 kg) |
| E650QC-7 | D | B, S | FB | QC | QC | SP, LR,BDP | 3.87 lbs. (1.8 kg) |
| E650QC-77 | D | B, S | FB | QC | QC | BL,SP,LR,BP,RB,BDP | 5.60 lbs. (2.5 kg) |
| E650DQC | D,P | B | FB | QC | QC | SP,LR,BDP | 3.45 lbs. (1.6 kg) |
| E650DQC-7 | D,P | B, S | FB | QC | QC | SP, LR,BDP | 3.87 lbs. (1.8 kg) |
| E650DQC-77 | D,P | B, S | FB | QC | QC | BL,SP,LR,BP,RB,BDP | 5.60 lbs. (2.5 kg) |



by Honeywell

Toll Free 800.873.5242 (press 4) • hsptechsupport@honeywell.com • www.millerfallprotection.com

WARNING! THIS DOCUMENT PROVIDES AN OVERVIEW OF FALL PROTECTION PRODUCTS AVAILABLE FROM HONEYWELL AND CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE DATA. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. HONEYWELL RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THE PRODUCTS BE THOROUGHLY READ AND UNDERSTOOD PRIOR TO EACH USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.