

### Multi-Purpose - SWX00320 (Medium)

## Description

- Organic Vapor & Acid Gas with P100 (Organic Vapor, Sulfur Dioxide, Hydrogen Chloride, Chlorine, All Particulates)
- NIOSH Approved
- Soft Thermal Plastic Elastomer (TPE) facepiece for enhanced comfort
- Includes a unique "Hygiene Guard" for clean storage and product protection
- Easy to adjust, comfortable head strap
- Lightweight, well contoured face seal for enhanced comfort and fit
- Easy positive pressure seal check
- Bayonet connection is compatible with Safety Works filters
- APF 10\* when properly fit tested and used with compatible filters and cartridges

\*APF (Assigned Protection Factors) and product compatibility are only effective when the employer implements a continuing, effective respirator program as required by Section 29 CFR 1910.134, including training, fit testing, maintenance and use requirements.

OSHA's Standard for Respiratory Protection, 29 CFR 1910, 134, requires Employers to implement a change schedule for all canisters and cartridges when there is not an end of service life indicator on the cartridge or canister. The employer shall describe the respirator program the information and data relied upon and the basis for the canister and cartridge change schedule and the basis for reliance on the data. This schedule must be site specific and take into consideration worksite humidity, worker breathing rate as well as contaminant concentrations.



## Technical Data

Material	Thermal Plastic Elastomer (TPE)
Color	Blue
Sizes	Medium
Packaging	1 mask per clamshell, 5 clamshells per case
Case Dimensions	24.0" x 11.4" x 10.8" / 61.0cm x 29.0cm x 27.4cm
Case Weight	5.5 lbs / 2.5 kg
COO	China

## Barcodes

Item	Clamshell	Case
SWX00320	848309010135	10848309010132



RETAIL PACKAGED  
(CLAMSHELL)