

Miller DuraFlex[®] Python ULTRA

P950QC Series



by Honeywell

Description

DuraFlex Python[®] ULTRA, available in green or blue, is a stretchable full-body harness with friction buckle shoulder straps, quick connect leg buckles, quick connect chest strap buckle, sliding back D-ring, sub-pelvic strap, tool belt loops, Comfort-touch back D-ring pad and pull-free lanyard rings.

Also available in blue polyester webbing for greater chemical resistance. (Model P950DQC/UBL)



Materials

Webbing (DuraFlex)	Polyester, Urethane Elastomer
Webbing	1-3/4" Dacron polyester
Minimum Tensile Thread	5000 lbs. on webbing 6 cord bonded 3 strand polyester thread. Minimum tensile of 42 lbs.
Grommet Hardware	Brass Steel
D-Rings	5000 lbs. (22kN)
Buckles	4000 lbs. (18kN)
Label Materials	Lexan and Valeron
Label Contents	Bar Coding, Inspection, Type, Model, Date, Serial No., Material Specs, Size, Capacity, Certifications.

* All hardware meets ASTM (50) fifty-hour salt spray test requirements.

Technical

Max. Working Load	400lbs (181.4kg)
Webbing Min.Tensile	5000lbs (22kN)
D-ring Min. Tensile	5000lbs (22kN)
Buckle Min. Tensile	4000lbs (18kN)

Certification

Meets or exceeds all OSHA, ANSI, and CSA specifications.

P950QC
Shown



Additional Features are indicated within the harness Catalog Number.

Model No.	Web Type	D-Rings	Shoulder Straps	Leg Straps	Chest Strap	Special Features	Weight
P950QC	DP	B	FB	QC	QC	SP, LR	3.15 lbs. (1.4 kg)
P950QC-7	DP	B, S	FB	QC	QC	SP, LR	3.75 lbs. (1.7 kg)
P950QC-77	DP	B, S	FB	QC	QC	BL,SP,LR,BP,RB	5.60 lbs. (2.5 kg)
P950DQC	DDP	B	FB	QC	QC	SP,LR	3.15 lbs. (1.4 kg)
P950DQC-7	DDP	B, S	FB	QC	QC	SP, LR	3.75 lbs. (1.7 kg)
P950DQC-77	DDP	B, S	FB	QC	QC	BL,SP,LR,BP,RB	5.60 lbs. (2.5 kg)

Refer to next page for harness description keys.

Miller DuraFlex[®] Python ULTRA

P950QC Series

Shoulder/Leg Buckles

FB = Friction Buckles

MB = Mating Buckles

TB = Tongue Buckles

D-Rings

B = Sliding Back D-Ring

FD = Front D-Ring

F = Front O-Ring

H = Shoulder D-Rings

S = Side Positioning D-Rings

W = Sliding Back web D-Ring

X = D-Ring Web Extension

Webbing

D = DuraFlex Stretchable Webbing

DP = DuraFlex Python Webbing

DDP = Dacron Python Webbing

K = Kevlar Webbing

N = Nylon Webbing

P = Polyester Webbing

Special Features

AB = Attached Waist Belt

AL = Adjustable Belt Loops

BL = Belt Loops

BP = Back Pad

HP = Shoulder Pads

LP = Leg Pads

LR = Lanyard Ring

RB = Removable Waist Belt

SP = Sub-Pelvic Strap

SR = Self Rescue Loops

SS = Saddle Seat

TO = Tool Belt Buckles



by Honeywell

Toll Free 800.873.5242 (press 4) • hsptechsupport@honeywell.com • www.millerfallprotection.com

⚠ WARNING! THIS DOCUMENT PROVIDES AN OVERVIEW OF FALL PROTECTION PRODUCTS AVAILABLE FROM HONEYWELL AND CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE DATA. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. HONEYWELL RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THE PRODUCTS BE THOROUGHLY READ AND UNDERSTOOD PRIOR TO EACH USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.