# **CP 327**



# **BLUE CONTAINMENT TAPE**

#### TYPICAL APPLICATIONS

- For building containments in restoration, remodeling, remediation and abatement jobs
- Can be used on interior and exterior walls, glass, vinyl, metal and wood

#### **PRODUCT FEATURES**

- · Excellent adhesion to painted surfaces
- Prevents lifting that could result in containment failure
- Easy, no-residue removal
- Removes cleanly for up to 21 days without surface damage

# CONSTRUCTION

Overall Grade/Function: Specialty Containment Backing: Fine structured crepe paper Adhesive: Synthetic rubber-based

#### STANDARD WIDTH(S)

36 mm 48 mm 72 mm

# STANDARD LENGTH(S)

55 m Contact your Shurtape sales representative for other available sizes

# STANDARD CORE SIZE

3 in

# STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

#### COLOR(S)



PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	21 Ibs/in width	36.8 N/10 mm
Adhesion to Stainless Steel	32 oz/in width	3.50 N/10 mm
Thickness	5.4 mils	0.14 mm
Elongation	10%	10%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.



Shurtape Technologies, LLC | PO BOX 1530 Hickory, NC 28603-1530 USA | Phone 1.888.442.TAPE (8273) | Fax 800.335.7651 | shurtape.com ISO 9001 CERTIFIED QUALITY SYSTEM