



SKU # H4-LED-G2-KIT

Part # 1002007

Description

Discontinued - Superseded by Part #H4-G4LED

Categories HID & LED Headlights, LED Headlight Conversions

Sub-Categories LED Conversion Kits, Gen2 LED Headlight Kits

UPC 812867023128

Unit of Measure Kit

Related Skus:

RSSH4, RS-2RES-CON-H4

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Gen2 LED Headlight Kit

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

9-24VDC

Current Draw

3A

Wattage

35-Watts

Chip Type

IP Rating

IP67

LUX

2,600 LUX

Est. Labor

Hours

Gross Weight

1.20

Width

8.00

Net Weight

1.20

Height

2.50

DIM Weight

1.15

Depth

8.00

Kelvin (ColorTemperature)

5,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

No Warranty

Lumens

3,200lm

Beam Pattern

N/A



Product Information

The Next Generation in LED Headlight Technology Race Sport Lighting's LED Headlight Kit stomps the competition with over 3000 Lumens of output and an low 3 Amp current draw. Generation 2 goes the extra mile with an more focused beam pattern for brighter more controlled light output, wide input voltage range for a variety of vehicles and aluminum thermal core technology to maintain cooler operating temperatures. Easy to install kit comes with two-Year Warranty, 2 LED headlights, 2 built-in fans and 2 drivers. Priced per kit. • Improved cooling design • 2-3 times further vision than standard halogen bulbs • Instant On Technology provides full power light immediately • 5500 Kelvin • 35W operating power • Operating voltage range: 9V-24V • 3000 Lumen (2600lux)- 30% more luminous than Gen 1 Kits • 2 Year Warranty