



SKU # MS16FTWSTRIP-RGB

Part # 1003238

Description

RGB Multi-Color 16ft Flexible Strip Light w/ Clear Waterproof Sleeve IP67

Categories Marine, Marine Sport Lighting

Sub-Categories

Completely Waterproof LED Strip Lighting underneath boat, Waterproof Strip Lighting

UPC 812867027140

Unit of Measure EA

Related Skus:

MS24FTWSTRIP-RGB

Cross Sell Skus:

Condition

New

Manufacturer

Marine Sport Lighting

EZ Category

Weatherproof Strip Reels

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product

Marine All-Around Light

Part Type ID 57170

Reverse Polarity

Marine All-Around Light

Operating Voltage

Current Draw

Wattage

Chip Type

EPISTAR

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Linear



Product Information

- 12VDC operation • 5050SMD LEDs • 120 degree light spread • IP67 Rated marine grade strip. • Includes remote and controller • Can be cut into 3-LED segments • 3x brighter than standard 3528SMD LEDs • 1 Year Warranty

Est. Labor

0.5 Hours

Gross Weight

0.80

Width

8.00

Net Weight

0.80

Height

2.00

DIM Weight

1.18

Depth

10.25

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov