



SKU # MS80WSRS

Part # 1007242

Description

New - 18.25inch Marine Grade Single Row Straight Light Bar with 80-Watt 8 x 10W High Intensity OSRAM LEDs



Categories Marine, Marine Sport Lighting

Sub-Categories

Marine Sport® Heavy Duty Single Row LED Light Bars, Marine Series Light Bars

UPC 817999028713

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Marine Sport Lighting

EZ Category

Marine Single Row Straight Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

12-32VDC

Current Draw

6.3A

Wattage

80-Watts

Chip Type

IP Rating

IP67

LUX

Product Information

The NEW Marine Sport LED Light Bars are a revolutionary way to contour light bars and high power light output to any surface area with a straight or curve appeal. The light bars are designed for Marine use, but can also be used in Automotive, UTV, ATV, Industrial applications where a white colored shell is desired. To make these bars even more attractive, Race Sport uses a white facing tile instead of the common chrome tiles to give this a TRUE "WHITE OUT" look! We use durable and long lasting CREE 3-watt diodes in these bars and recess them in our long throw opticals for a maximum performance and light output! . Operating Voltage: 9-30V DC 10 watt OSRAM . Color Temperature: 6000K . Lens material: PC . Optional Beam: Combo . Waterproof to 1M Rate: IP67 . Optional Color: Black . Material: Aluminum alloy painting . Mounting Bracket: Alu firm bracket . 50000+ hours life-span 18.25in End-to-End 16in Lens Width Area 19.50in Mounting Hole to Mounting Hole 3.0in Height 3.50in Depth Note*

Est. Labor 1 Hours

Gross Weight 5.56 **Width** 5.25

Net Weight 4.94 **Height** 6.00

DIM Weight 5.50 **Depth** 24.25

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

5,600lm

Beam Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov