



SKU # MSPS12WSRG

Part # 1007458

Description

12V-24V Marine Starboard GREEN and Port RED LED light set with White Shell

Categories Marine Sport Lighting

Sub-Categories Navigation Signal LED's

UPC 810077230497

Unit of Measure PR

Related Skus:

MSPS12BSGR

Cross Sell Skus:

MSSOLAR4

Condition

New

Manufacturer

Marine Sport Lighting

EZ Category

Marine Navigation Light Systems

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Marine Bow Light

Part Type ID 57169

Reverse Polarity

Marine Bow Light

Operating Voltage

12-24VDC

Current Draw

0.5-2.0A

Wattage

1.5 Watts

Chip Type

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

Red/Green

Universal or Vehicle Specific

Universal

Made In

CN

Warranty

1 year

Lumens

Beam Pattern



Product Information

Voltage:12V/24V Type: LED Power: 1.5W Material: White ABS Screw Mount System 2-Wire Power Ground System Teardrop Design 8-LED Diode System

Est. Labor

Hours

Gross Weight

0.40

Width

2.50

Net Weight

0.40

Height

3.75

DIM Weight

0.27

Depth

4.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com