



SKU # MSUWBTC12V

Part # 1006994

Description

NEW - HydroBLAST Marine Bluetooth RGB Multicolor Controller with 2 RGB Outputs - 360-Watts DC12V input/output



Categories Marine Sport Lighting

Sub-Categories HydroBLAST Underwater LED

UPC 817999026399

Unit of Measure EA

Related Skus:

MS-27RGB, MSUWL60RGB, MSUWL120RGB, MSUWL180RGB, MSUWUS60RGB, MSUWUS30RGB

Cross Sell Skus:

Condition

New

Manufacturer

Marine Sport Lighting

EZ Category

HydroBLAST Marine LED

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product

Wireless Connection Remote Control Switch

Part Type ID 49762

Reverse Polarity

Wireless Connection Remote Control Switch

Operating Voltage

12-24VDC

Current Draw

18A

Wattage

360-Watts

Chip Type

N/A

IP Rating

IP68

LUX

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China

Warranty

2 year

Lumens

Beam Pattern

N/A

Product Information

Input voltage DC 12V or 24V output power Max-360W IP67 Waterproof rating Aluminum body LED BLE is the app for the Bluetooth Comes with two output connections for easy install on external pods and interior lighting.

HydroBLAST series by Marine Sport Lighting



Est. Labor

0.5 Hours

Gross Weight

2.00

Width

7.50

Net Weight

2.00

Height

2.50

DIM Weight

0.71

Depth

5.25

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com