



**SKU # MSUWRCC12V**

**Part # 1006988**

Description

NEW - HydroBLAST Marine Remote Controlled RGB Multicolor Controller with 2 RGB Outputs - 240-Watts DC12V input/output



**Categories** Marine Sport Lighting

**Sub-Categories** HydroBLAST Underwater LED

**UPC** 817999026405

**Unit of Measure** EA

**Related Skus:**

MS-27RGB, MSUWL60RGB, MSUWL120RGB, MSUWL180RGB, MSUWUS60RGB, MSUWUS30RGB

**Cross Sell Skus:**

**Condition**

New

**Manufacturer**

Marine Sport Lighting

**EZ Category**

HydroBLAST Marine LED

**Harmonization Code**

8512.20.2080

**Universal**

YES

**Life Expectancy**

50,000 hours

**SEMA Product**

Wireless Connection Remote Control Switch

**Part Type ID** 49762

**Reverse Polarity**

Wireless Connection Remote Control Switch

**Operating Voltage**

12-24VDC

**Current Draw**

12.5A

**Wattage**

216-Watts

**Chip Type**

N/A

**IP Rating**

IP68

**LUX**

**Kelvin (ColorTemperature)**

RGB

**Universal or Vehicle Specific**

Universal

**Made In**

China

**Warranty**

2 year

**Lumens**

**Beam Pattern**

N/A

**Product Information**

IP67 Rated Marine Remote Controlled RGB Multicolor Controller with 2 RGB Outputs - 240-Watts DC12V input/output. The controller is a touch button RF remote.

**Est. Labor**

0.5 Hours

**Gross Weight**

2.00

**Width**

9.00

**Net Weight**

2.00

**Height**

2.50

**DIM Weight**

0.81

**Depth**

5.00