



SKU # MS-MRDR06

Part # 1003207

Description

8" Dual Row LED HD Marine Grade Light Bar

Categories Marine, Marine Sport Lighting

Sub-Categories

Marine Sport® Heavy Duty Dual Row LED Light Bars, Marine Series Light Bars

UPC 812867027027

Unit of Measure EA

Related Skus:

Cross Sell Skus:

RSTP016

Condition

New

Manufacturer

Marine Sport Lighting

EZ Category

Marine Sport Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

9-32VDC

Current Draw

1.9-23.8A

Wattage

36-Watts

Chip Type

CREE

IP Rating

IP68

LUX

Est. Labor

1 Hours

Gross Weight

4.00

Width

5.25

Net Weight

4.00

Height

5.25

DIM Weight

2.83

Depth

14.25

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

Lifetime

Lumens

2,520lm

Beam Pattern

Combo



Product Information

Looking for increased visibility while docking your boat? Wish your boat's deck was illuminated better at night? Marine Sport® Lighting's marine grade dual row LED light bars are the perfect solution for providing a blast of light wear you need it, when you need it. Marine Sport Lighting's MS-MRDR06 marine grade dual row LED light bars feature high power CREE diodes producing 2,520 lumens of output power which means extended family activity time on the water and increased safety docking your boat when the fun is done. These light bars are equipped with a combination of spot and flood optics which means you get excellent projection distance without forfeiting functional width of the beam pattern. The MS-MRDR06 is fastened with a rubber grommet and injection sealant to provide IP68 rated defense against water intrusion and environmental attack which means you can land that fish no matter the weather conditions. We also coated the light bar with a durable powder coat and additi