



SKU # PSX26W-G4LED

Part # 1007551

Description

PSX26W GEN4® LED Headlight Conversion Kit with Focus Optics, and copper stranded rope heat sinks - Patent Approved Design



Categories LED Headlight Conversions

Sub-Categories GEN4® LED Kits

UPC 810077230893

Unit of Measure Kit

Related Skus:

RSCAS004

Cross Sell Skus:

RSIKIT,RSUKIT,RSMKIT

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

GEN4 LED Headlight Kit

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

12VDC

Current Draw

3.2A

Wattage

Chip Type

PHILLIPS

IP Rating

IP65

LUX

7,004 RAW LUX

Est. Labor

1 Hours

Gross Weight

1.00

Width

8.25

Net Weight

0.75

Height

2.50

DIM Weight

1.11

Depth

7.50

Kelvin (ColorTemperature)

6,000K

Universal or Vehicle Specific

Universal

Made In

CN

Warranty

3 year

Lumens

6,330 RAW LUMEN

Beam Pattern

N/A

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com