



SKU # RS1157HPW

Part # 1005049

Description

1157 BLAST Series Hi Power 30W CREE LED Replacement Bulbs - PAIR (WHITE)



Categories

Auto Interior & Exterior, Agricultural, Motorcycle, LED Replacement Bulbs

Sub-Categories

LED Replacement Bulbs, Blast Series Hi Power LED Replacement Bulbs , BLAST Series High-Powered CREE LED Bulbs, Blast Series LED Replacement Bulbs

UPC 817999020328

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

BLAST LED Bulbs

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Turn Signal Light

Part Type ID 2872

Reverse Polarity

Turn Signal Light

Operating Voltage

12-24VDC

Current Draw

Wattage

30-Watts

Chip Type

IP Rating

LUX

Product Information

Blast Series LED replacement bulbs are perfect for vehicle reverse lights, but are available in every common base to fit your needs. Featuring up to 15 high-power LEDs, the radially mounted LEDs emit a 360° viewing angle, and a forward-facing projector lens produces an intense spot beam pattern for long-range illumination. • Easy plug-and-play installation • 50,000 hours lifetime—25 times longer than incandescent bulbs • 6,500K Cool White • Sold in pairs

Est. Labor

0.2 Hours

Gross Weight

0.10

Width

3.25

Net Weight

0.10

Height

5.00

DIM Weight

0.03

Depth

0.25

Kelvin (ColorTemperature)

White

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com