



SKU # RS120-WA

Part # 1004997

Description

21.5in Wrap Around ECO-LIGHT LED Light Bars w/ 3D Reflector Optics - Hot Seller

Categories Truck, Powersports, LED Light Bars

Sub-Categories

LED Light Bars, Wrap Around ECO-LIGHT LED Light Bars with 3D Reflector Opticals, Eco Series Dual Row Light Bars

UPC 814843021876

Unit of Measure EA

Related Skus:

Cross Sell Skus:

RSTP016

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ECO Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

9-16VDC

Current Draw

9.5A

Wattage

120-Watts

Chip Type

CREE

IP Rating

IP67

LUX

Est. Labor

1 Hours

Gross Weight

6.50

Width

6.25

Net Weight

5.75

Height

5.25

DIM Weight

5.67

Depth

24.00

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

7,800lm

Beam

Pattern

Combo



Product Information

Race Sport Lighting's ECO-Light series LED light bars feature proprietary optics for unmatched light output, all at an economical price point making them our premier entry level LED bar. • 120W • 9.5 AMPs • 7,800 Lumens • Combination light pattern • 9-16v Voltage Range • 22" Bar Length End-to-End • 25" Bar Length including Mount • 1 Year Warranty

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com