



SKU # RS1806

Part # 1006815

Description

6-switch LED Logo Rocker Panel with Digital Voltage Gauge and Pre-wired harness kit - Fits Jeeps direct, and other vehicles with slight modifications

Categories LED SWITCHES, LED Switches, Marine Sport Lighting

Sub-Categories

Switch All-in-One Systems, LED Illuminated Logo Rocker Switches, LED Illuminated Logo Rocker Switches

UPC 817999024999

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Switch Panel System

Harmonization Code

8512.20.2080

Universal

No

Life Expectancy

50,000 hours

SEMA Product

Rocker Switch and Cover Set

Part Type ID 20511

Reverse Polarity

Rocker Switch and Cover Set

Operating Voltage

12VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

N/A

Universal or Vehicle Specific

Vehicle Specific

Made In

China

Warranty

1 year

Lumens

Beam Pattern



Product Information

This system will control all of your lights on any vehicle. Just mount, wire, power, and control all your auxiliary lights and other 12 volt devices even. 12-volt system includes all wiring and mounting hardware Direct fit for 07-17 JEEP JK's - Universal with slight modification for other vehicles. - Voltage range : DC12-24V -About 8.86 x 2.72 x 2.17 inch - Two hole distance:8.31x2.17inch -Overload protection: 12V 20A DC; 24V 10A DC4-Rugged aluminum with black texture powder coating painting finish - Operating Temperature: -25 degree to 80 degree -Short circuit protection, overload protection & reverse polarity protection -Voltmeter monitor the battery voltage and battery voltage state

Est. Labor

Hours

Gross Weight

8.70

Width

11.75

Net Weight

8.70

Height

6.50

DIM Weight

6.46

Depth

11.75