



**SKU # RS288**

**Part # 1005027**

Description

50in ECO-LIGHT LED Light Bars w/ 3D Reflector Optics & CREE LED



**Product Information**

Race Sport Lighting's ECO-Light series LED light bars feature proprietary optics for unmatched light output, all at an economical price point making them our premier entry level LED bar. • 288W • 22.8 AMPs • 19,000 Lumens • Combination light pattern • 9-16v Voltage Range • Bar Height: 3" (75.75mm) • Mounted Height (Level to Mounting Surface): 4" (101.875mm) • 50" Bar Length End-to-End • 52" Bar Length including Mount • 1 Year Warranty

**Categories** Truck, Powersports, Truck, LED Light Bars

**Sub-Categories**

LED Light Bars, Straight ECO-LIGHT LED Light Bars with 3D Reflector Opticals, LED Light Bars, Eco Series Dual Row Light Bars

**UPC** 814843021845

**Unit of Measure** EA

**Related Skus:**

RSTP016, RS-HARN-SS2

**Cross Sell Skus:**

RS3X3ECO,RS3X3FECO

**Est. Labor**

1 Hours

**Gross Weight**

16.00

**Width**

5.25

**Net Weight**

16.00

**Height**

6.00

**DIM Weight**

11.84

**Depth**

52.25

**Condition**

New

**Manufacturer**

Race Sport Lighting

**EZ Category**

ECO Series Light Bars

**Harmonization Code**

8512.20.2080

**Universal**

YES

**Life Expectancy**

50,000 hours

**SEMA Product** Light Bar

**Part Type ID** 1069

**Reverse Polarity**

Light Bar

**Operating Voltage**

9-16VDC

**Current Draw**

22.8A

**Wattage**

288-Watts

**Chip Type**

PHILLIPS

**IP Rating**

IP67

**LUX**

**Kelvin (ColorTemperature)**

6,500K

**Universal or Vehicle Specific**

Universal

**Made In**

China

**Warranty**

1 year

**Lumens**

19,000lm

**Beam**

Pattern

Combo

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)