



SKU # RS3020BSP

Part # 1006758

Description

WHITE-AMBER Strobe Pro Series 4-LED Ultra thin style marker strobes with stylish clear lens face - Self Strobing pattern settings

Categories Commercial, Commercial, Strobe Lighting Kits

Sub-Categories

Surface Mount LED Strobe Marker Lights, Super Slim Flush Mount LED Strobe Marker Lights, StrobePro Surface Mount Marker Lights

UPC 817999024579

Unit of Measure EA

Related Skus:

RSMSPLATE

Cross Sell Skus:

RS7003AWD,RS826WA,RS-281-4LED-WA,RS-35L21D-TBD-A

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Strobe PRO Series markers

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product Strobe Light Kit

Part Type ID 17809

Reverse Polarity

Strobe Light Kit

Operating Voltage

12VDC

Current Draw

Wattage

Chip Type

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

White/Amber

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern



Product Information

• 4 LED surface mount light head • ECE R65 Single flash, ECE R10, • New Slim Led Light Head-- SAE/ECE R65 R10 • SAE J595 CLASS1 Double Flash • IP 67 • 3W each LED • Five cables,19 flash patterns • With memory function • DC 12V~24V 3 7/8 Length 1 1/4 Wide

Est. Labor

Hours

Gross Weight

0.00

Width

1.75

Net Weight

0.00

Height

1.50

DIM Weight

0.10

Depth

5.25

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com