



SKU # RS3TEMPCL

Part # 1007573

Description

20-Watt 2,000lm RoadRunner Compliant IP67 Cube Aux Light with SPOT MELT Temp Control System and frameless construction

Categories LED Light Bars, LED Spots and Auxiliary Lighting

Sub-Categories

ROADRUNNER SERIES ON-ROAD COMPLIANT LIGHT BARS, Heavy Duty Spot Lights & Accessories

UPC 810077230213

Unit of Measure EA

Related Skus:

RS7TEMPFM, RS6TEMPAL

Cross Sell Skus:

RS7TEMPLB,RS50TEMPLB,RS32TEMPLB,RS10TEMPLB,RS40TEMPLB,RS20TEMPLB

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

RoadRunner Series

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Off-Road Light

Part Type ID 15431

Reverse Polarity

Off-Road Light

Operating Voltage

10-30VDC

Current Draw

1.5 Amps

Wattage

20-Watts

Chip Type

OSRAM

IP Rating

IP67

LUX

Est. Labor

1 Hours

Gross Weight

1.00

Width

4.25

Net Weight

1.00

Height

5.00

DIM Weight

0.61

Depth

4.00

Kelvin (ColorTemperature)

5,700K

Universal or Vehicle Specific

Universal

Made In

CN

Warranty

2 year

Lumens

1,920 lm

Beam

Pattern

Spot



Product Information

. LED Power: 20W . Raw Lumen:1920lm . Operating Voltage: 10-30V DC . Waterproof rate: IP 67 . 4pcs*5W high intensity OSRAM LED . Current draw:1.5A@12V,0.75A@24V . Color Temperature: 5700K . Material: Diecast aluminum housing . Lens material: PC . Mounting Bracket: Metal Plate . Beam: Spot . LED Life-Span: 50,000 hours . Certificates: CE/ IP69K/ RoHS/ IP67 . Cool black, frameless, hooded reflector design . With TCS Temp Control System (No ice)

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com