



SKU # RS3X3ECO

Part # 1006996

Description

NEW - ECO-LIGHT LED High Power CUBE Style Auxiliary Lights (Sold as Pairs)

Categories LED Light Bars, LED Light Bars

Sub-Categories Eco Series Dual Row Light Bars, ECO-SLIM Single Row Light Bars

UPC 817999026191

Unit of Measure PR

Related Skus:

RSLEDH2, RS-SS-HARN

Cross Sell Skus:

RS3X3FECO,RS36,RS120

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ECO Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product Off-Road Light

Part Type ID 15431

Reverse Polarity

Off-Road Light

Operating Voltage

9-16VDC

Current Draw

4A

Wattage

Chip Type

PHILLIPS

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

5,900 Lm

Beam Pattern

Spot



Product Information

These amazing pair of ECO-SERIES LED cubes will give users the brightness and durability in auxiliary lights they are looking for. These super high power auxiliary work lights are the perfect solution for your work light needs. Unlike most cubes on the market, these revolutionary cubes give off two types of beam patterns that give you maximum light spread to complete the job. . LED Power: 48W . Dimensions: 3.0 inch . Operating Voltage: 10-30V DC . 16pcs*3w high intensity 3030 LEDs . Optional Color: Black Shell . Color Temperature: 6000K . Material: Diecast aluminum housing . Lens material: PMMA . Mounting Bracket: Stainless Steel . COMBO Beam: Pencil + spot . 30,000 hours above life time . Waterproof rate: IP67

Est. Labor 1 Hours

Gross Weight 1.90 **Width** 5.25

Net Weight 1.90 **Height** 4.00

DIM Weight 1.21 **Depth** 8.00