



SKU # RS4PRGBW

Part # 1006962

Description

NEW 4-POD RGBW Hi-Power Rock Light Complete Kit with Bluetooth APP controls in Retail Box



Categories LED Rock Light Kits, Jeep

Sub-Categories LED Glow POD Station Lights (Rock Lights)

UPC 817999026498

Unit of Measure Kit

Related Skus:

RSRL3EXT5, RS6PRGBW, RS8PRGBW

Cross Sell Skus:

RSIKCS

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

RGB+W Rock Light Kits

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product Wheel Accent Light

Part Type ID 15452

Reverse Polarity

Wheel Accent Light

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

IP68

LUX

Kelvin (ColorTemperature)

RGB+W

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Product Information

Even better than RGB Rock Lights, are RGB+W Rock Light Kits! Enjoy our super durable rock lights kits now with a 4th LED Diode on the circuit board to enjoy a pure white hi power diode! Kits available in 4, 6, 8 and now 12 piece rock light kits. All kits are controlled by our Bluetooth Smart Phone application and Color Wheel options! All Lights, Hardware and instructions included in the kit to complete the job. Some longer vehicles may need extension cables.

Est. Labor

3 Hours

Gross Weight

2.01

Width

7.75

Net Weight

2.01

Height

5.50

DIM Weight

1.61

Depth

5.25

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com