



### SKU # RS7TEMPFM

Part # 1007452

#### Description

7in 30-Watt RoadRunner Compliant IP67 Flush Mount 3,000lm Aux Spot Light with MELT Temp Control System and frameless construction



**Categories** LED Light Bars

**Sub-Categories** ROADRUNNER SERIES ON-ROAD COMPLIANT LIGHT BARS

**UPC** 810077230237

**Unit of Measure** EA

#### Related Skus:

RS6TEMPAL, RS3TEMPCL, RS7TEMPFM-F

#### Cross Sell Skus:

RS7TEMPLB,RS50TEMPLB,RS32TEMPLB,RS10TEMPLB,RS40TEMPLB,RS20TEMPLB

#### Condition

New

#### Manufacturer

Race Sport Lighting

#### EZ Category

RoadRunner Series

#### Harmonization Code

8512.20.2080

#### Universal

YES

#### Life Expectancy

50,000 hours

**SEMA Product** Off-Road Light

**Part Type ID** 15431

#### Reverse Polarity

Off-Road Light

#### Operating Voltage

10-30VDC

#### Current Draw

2.04A

#### Wattage

30-Watts

#### Chip Type

OSRAM

#### IP Rating

IP67

#### LUX

#### Kelvin (ColorTemperature)

5,700K

#### Universal or Vehicle Specific

Universal

#### Made In

CN

#### Warranty

2 year

#### Lumens

2,880lm

#### Beam Pattern

Spot

#### Product Information

. LED Power: 30W . Raw Lumen:2880lm . Operating Voltage: 10-30V DC . Waterproof rate: IP 67 . 6pcs\*5W high intensity OSRAM LED . Current draw: 12V/2.04A; 24V/1.04A . Color Temperature: 5700K . Housing: 6.18"x1.72"x2.36"Cast Aluminum . Lens material: PC . Mounting Bracket: Stainless Steel . Beam: Spot .LED Life-Span: 50,000 hours .Certificates: CE/ IP69K/ RoHS/ IP67 . Cool black, frameless, hooded reflector design . With TCS Temp Control System

#### Est. Labor

1 Hours

#### Gross Weight

1.50

#### Width

3.50

#### Net Weight

1.50

#### Height

3.50

#### DIM Weight

0.77

#### Depth

8.75

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)