



SKU # RS8195FT

Part # 1006819

Description

5-Foot Long ColorADAPT Chasing RGB Multi-Color Whip with Remote Control and over 150+ Patterns



Categories LED Flagpole Whips, ColorADAPT RGB LED Accent Kits

Sub-Categories

UPC 817999025064

Unit of Measure EA

Related Skus:

RS8195FTBT

Cross Sell Skus:

RS8PRGBW,RSRGB15-C,RS5M5050IP67-C

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ColorADAPT RGB Product

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product Lighted Whip

Part Type ID 58857

Reverse Polarity

Lighted Whip

Operating Voltage

12VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Product Information

These amazing NEW whips are stronger, better, and more functional than previous generations! Boasting over 150+ different strobe, running, and chasing modes to brag to your friends. The whip has a super thick base and diameter with more bendable material that allows this whip to take a real beating while you are out having fun. At the end of the ride, it contains a quick disconnect that you can take the whip off as you trailer it back and forth from home. The RGB+W allows tons of color combinations and patterns that will mind boggle the spectators. Be noticed while riding!

Est. Labor

1 Hours

Gross Weight

3.01

Width

2.00

Net Weight

3.01

Height

60.75

DIM Weight

1.97

Depth

2.25

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov