



SKU # RSBAY15DSBWA

Part # 1006856

Description

1157 (BAY15D) NO-RAPID FLASH Canbus Turn signal LED Bulbs - Switchback version in White / Amber 9v-30v 1860lumens Epistar 3030 (Sold as Pair)

Categories

LED Replacement Bulbs, LED Replacement Bulbs, LED Replacement Bulbs

Sub-Categories

NO-RAPID Series Canbus Turn Signals Bulbs, Switchback Dual-Color LED Replacement Bulbs, No-Rapid Series

UPC 817999025231

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

NO-RAPID Series LED Bulbs

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product Turn / Park Light Bulb

Part Type ID 47458

Reverse Polarity

Turn / Park Light Bulb

Operating Voltage

12-24VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

White/Amber

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern



Product Information

Tired of LED Turn Signal Bulbs flashing rapidly? Tired of putting those Super HOT golden resistors in to stabilize the flash? Then Race Sport Lighting's new NO-RAPID Series LED replacement turn signals are the solution for you. Not only does their circuitry regulate the flash pattern, but they are CANBUS ready to plug n'y play.

Est. Labor

0.3 Hours

Gross Weight

0.10

Width

3.00

Net Weight

0.10

Height

4.50

DIM Weight

0.10

Depth

1.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com