



SKU # RSIKCS

Part # 1005210

Description

LED Interior RGB Multi-Color Accent Kit ColorSMART Smartphone Controlled with millions of colors and patterns

Categories

Marine, Golf Cart Lighting, Auto Interior & Exterior, ColorSMART RGB Bluetooth LED Accent Kits

Sub-Categories

LED Accent Lighting Interior, Interior Accent Lighting, RGB Complete Kits

UPC 814843029940

Unit of Measure Kit

Related Skus:

RS12EW, RS3EW, RSIKIT

Cross Sell Skus:

RSRGB15-C

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ColorSMART Bluetooth RGB Products

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

12VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern



Product Information

ColorSMART's smartphone control allows you to:

- Select any color via color wheel and RGB sliders
- Change modes between fade, flash, loop, or music sync
- Power your strips on and off without looking for your remote
- ColorSMART is supported on Android & Apple devices
- ColorSMART Interior Accent Kits include: -Four 10" water-resistant flexible RGB LED strips with 3M adhesive backing -Wiring extensions -Bluetooth RGB LED controller
- Requires proprietary app to use. Scan QR code cards in box to download these from the App Store or Google Play Store
- 1 Year Warranty Can only be used with a Bluetooth enabled smartphone or tablet, standalone remotes are not available. Use the free app 'Happy Lighting' on Android or iOS. The driver should adjust the controller only when the vehicle is stopped. Only a vehicle passenger should adjust the controller while the vehicle is moving. It is your responsibility to comply with all traffic laws.

Est. Labor

1 Hours

Gross Weight

1.05

Width

11.00

Net Weight

1.05

Height

2.25

DIM Weight

0.67

Depth

3.75

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov