



SKU # RSSS3X3PR

Part # 1005394

Description

Street Series 3x3in 16W 4-LED Cube Spot Lights w/ Amber Cover (Sold as Pair)

Categories

Truck, Marine, Powersports, Agricultural, LED Spots and Auxiliary Lighting

Sub-Categories

Auxiliary Spot & Floods, Marine Sport® Hi Power LED Spot Lights, STREET Series LED Spot Lights, STREET Series LED Spot Lights, Street Series Spot Lights & Accessories

UPC 814843025584

Unit of Measure PR

Related Skus:

RS-4L-3X316W, RS-4CREE-35W-2

Cross Sell Skus:

RSTP016

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Street Series Aux Spots

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Off-Road Light

Part Type ID 15431

Reverse Polarity

Off-Road Light

Operating Voltage

9-24VDC

Current Draw

2.66 Amps

Wattage

16-Watts

Chip Type

CREE

IP Rating

IP67

LUX

1,200LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

1,200 lm

Beam Pattern

Spot



Product Information

These twin Street series 16W (32-Watts Total) 3x3 LED Spot Lights come economically priced and attractively packaged. At 1,200 Lux a piece, these pairs give you almost 2,500 Lux of light output. Combine with the included amber spot covers, as well as the wide variety of mounting brackets Race Sport Lighting offers, these spots are perfect for fog lights or other auxiliary lighting. Kit Contents • (2) 3x3 Street Series 16W 4-LED Spot Lights • (2) Amber covers for 3x3 Spots Specifications • 50,000 hour life expectancy • 6,500 Kelvin • Spot Optics • 1,200 Lux per spot • 1.33 Amps/Light (2.66 Amps for Entire Kit) • Durable housing • 3 Year Warranty

Est. Labor	1 Hours	Gross Weight	3.20	Width	5.40
Net Weight	1.51	Height	9.50	Depth	4.10

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov