



SKU # RSTP016

Part # 1006817

Description

Remote Control Strobe Capable Wire and Switch Harness for Light Bars and Auxiliary lights - Solid or Strobe at the touch of a remote



Categories LED Light Bars

Sub-Categories Light Bar Harnesses

UPC 817999024975

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Light Bar Harness

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product

Strobe Light Control Module Connector

Part Type ID 49176

Reverse Polarity

Strobe Light Control Module Connector

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Product Information

This on/off strobe capable harness is amazing, and gives you maximum control over the auxiliary lights you hook up to it. 1-Voltage range : 12-24V Fuse : 30A 2-Output power : 15-300W 3-6 feet long (2 meters) 4-Remote control, can switch high/low beam,slowly strobe or flashing 5-Remote distance range : Long Rang 0-150 meter 6-UL1015-14AWG pure copper with PVC tube 7-whole set including wireless receiver,wireless controller, waterproofed fuse box,wire harness

Est. Labor

Hours

Gross Weight

0.02

Width

3.00

Net Weight

0.02

Height

2.00

DIM Weight

0.19

Depth

4.50

Kelvin (ColorTemperature)

N/A

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com