



SKU # RS-10W-750LM-W

Part # 1003749

Description

Rechargeable 10W/750 Lumen White Portable Work Light



Categories Work Tool Safety

Sub-Categories Lithium Rechargeable Work Lights

UPC 811712026420

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

LED Work Lights

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product

Portable Spotlight

Part Type ID

48854

Reverse Polarity

Portable Spotlight

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Product Information

The rugged water-resistant design of these rechargeable work lights allows them to go wherever the job takes you • 10W • Water resistant, rugged design • Rechargeable battery holds 6 hour charge • 750 Lumens • Wall and 12V car chargers • Durable CREE LED rated at 30,000 hours • 1 Year Warranty

Est. Labor

Hours

Gross Weight

2.40

Width

7.00

Net Weight

2.40

Height

6.50

DIM Weight

2.29

Depth

7.00

Kelvin (ColorTemperature)

White

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com