



**SKU # RS-16FT-3528-RGB**

**Part # 1003759**

Description

16ft (5M) 20-Color 3528 LED Strip w/ Remote (RGB Multi-Color) IP66

**Categories** Auto Interior & Exterior, LED Tape Strip Lighting

**Sub-Categories** LED Tape & POD strips, 3528 Consumer Tape Strip Reels

**UPC** 817363014236

**Unit of Measure** EA

**Related Skus:**

**Cross Sell Skus:**

**Condition**

New

**Manufacturer**

Race Sport Lighting

**EZ Category**

Interior Tape Strip LED

**Harmonization Code**

8512.20.2080

**Universal**

YES

**Life Expectancy**

**SEMA Product**

Interior Accent Light

**Part Type ID**

18826

**Reverse Polarity**

Interior Accent Light

**Operating Voltage**

**Current Draw**

**Wattage**

**Chip Type**

**IP Rating**

IP67

**LUX**

**Kelvin (ColorTemperature)**

RGB

**Universal or Vehicle Specific**

Universal

**Made In**

China

**Warranty**

1 year

**Lumens**

**Beam Pattern**

Linear



**Product Information**

Super bright, universal lighting solution for your home, office, business, or any other application • 120° viewing angle, perfect for any area • Able to be cut at 3 LED intervals (approximately every 2") for virtually any application • Maintenance free, easy installation • Improved adhesive backing for better, longer lasting application • 100,000+ hour lifetime • IP65 Water Resistant • 1 Year Warranty

**Est. Labor**

Hours

**Gross Weight**

2.20

**Width**

7.50

**Net Weight**

1.90

**Height**

2.00

**DIM Weight**

1.08

**Depth**

10.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)