



SKU # RS-27W-R

Part # 1003777

Description

Street Series 4" Round High-Powered LED 27W/1755LM (Each)

Categories LED Spots and Auxiliary Lighting, Agricultural, Powersports, Truck

Sub-Categories

Street Series Spot Lights & Accessories, STREET Series LED Spot Lights, STREET Series LED Spot Lights, Auxiliary Spot & Floods

UPC 811712020305

Unit of Measure EA

Related Skus:

Cross Sell Skus:

RSTP016

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Street Series Aux Spots

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Auxiliary Light

Part Type ID 1005

Reverse Polarity

Auxiliary Light

Operating Voltage

9-24VDC

Current Draw

Wattage

27-Watts

Chip Type

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

Red

Universal or Vehicle Specific

Universal

Made In

CN

Warranty

3 year

Lumens

1,755lm

Beam

Pattern



Product Information

Great as an off road work light, these 4" Round LED spots let out almost 2,000 Lumens of light output, more than enough for any purpose. • 27W/1,755LM (3W per diode) • 50,000 hour lifetime • 6,500 Kelvin color • Combination spot and flood optics • Durable spotlights, built to last • 3 year limited Warranty • Also sold in pairs

Est. Labor

1 Hours

Gross Weight

1.60

Width

5.00

Net Weight

1.60

Height

3.00

DIM Weight

0.70

Depth

6.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com