



## SKU # RS-42MM-5050CAN-W

Part # 1003828

### Description

42mm 5050 CANBUS LED (White) (Individual)

**Categories** Auto Interior & Exterior, LED Replacement Bulbs

### Sub-Categories

LED Replacement Bulbs, 5050 Canbus Series LED Replacement Bulbs

**UPC** 811712023535

**Unit of Measure** EA

### Related Skus:

### Cross Sell Skus:

### Condition

New

### Manufacturer

Race Sport Lighting

### EZ Category

5050 CANBUS LED Bulbs

### Harmonization Code

8512.20.2080

### Universal

YES

### Life Expectancy

**SEMA Product** Dome Light

**Part Type ID** 2772

### Reverse Polarity

Dome Light

### Operating Voltage

12-24VDC

### Current Draw

### Wattage

### Chip Type

### IP Rating

### LUX

### Kelvin (ColorTemperature)

White

### Universal or Vehicle Specific

Universal

### Made In

China

### Warranty

1 year

### Lumens

### Beam

### Pattern



### Product Information

Step it up and replace your stock bulbs with our professional grade 5050 LED replacement bulbs for brighter, crisper illumination Race Sport Lighting's LED Replacement Bulbs are available in a variety of bases and colors for virtually any application, and are the perfect solution to upgrade your interior or exterior automotive lighting • 1 Year Warranty

**Est. Labor** 0.1 Hours

**Gross Weight** 0.10 **Width** 2.25

**Net Weight** 0.10 **Height** 4.00

**DIM Weight** 0.03 **Depth** 0.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)