



SKU # RS-48-LEDBAR-S

Part # 1003842

Description

48in Standard 5-Function LED Tailgate Bar



Categories Truck, Truck LED Multi-Function Tailgate Bars

Sub-Categories Tailgate LED Bars, Standard Tailgate Bars

UPC 817363015295

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Truck Tailgate Light Bar

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Tailgate Light

Part Type ID 15288

Reverse Polarity

Tailgate Light

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Product Information

Race Sport Lighting Product Showcase: LED Tailg...



Utilizes high power 5050 LEDs for a brighter light, providing improved night safety • IP67 rated weatherproof silicone coating in an aluminum channel for a more durable bar in any environment • Full function tailgate bar serves as additional running, brake, reverse, and indicator lights • Simple no-drill mounting with 20kg rated industrial adhesive for a long lasting hold • Running, brake, and turn signal function are Plug-&Play, with simple one wire install for reverse function • Available in 60" a

Est. Labor

Hours

Gross Weight

2.40

Width

3.50

Net Weight

2.20

Height

50.00

DIM Weight

4.41

Depth

3.50

Kelvin (ColorTemperature)

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com