



SKU # RS-7-HID-35W

Part # 1003724

Description

Discontinued - 7in High-Powered HID Off Road Work Lamp 6500K (each)



Categories Agricultural, HID & LED Headlights, LED Spots and Auxiliary Lighting

Sub-Categories

HID Hi-Power Spot Lights, HID Conversion Kits, HID Sealed Beam Spot Lights

UPC 811712020756

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product Auxiliary Light

Part Type ID 1005

Reverse Polarity

Auxiliary Light

Operating Voltage

Current Draw

Wattage

35-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Product Information

High-Powered sealed beam HID lighting systems, great for work lights or off road lighting • Sealed HID ballast lighting system • Provides over 300% more visual light than halogen • Better vision provides you with longer viewing distances, increasing safety • 1 Year Warranty

Est. Labor

Hours

Gross Weight

3.20

Width

10.00

Net Weight

3.20

Height

7.50

DIM Weight

5.13

Depth

9.50

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

3,000lm

Beam Pattern

Flood

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com