



SKU # RS-9FT-5050-RGB

Part # 1003748

Description

9ft (3M) 20-Color RGB Multi-Color 5050 LED Strip w/ Remote



Categories Auto Interior & Exterior, LED Tape Strip Lighting, Marine Sport Lighting

Sub-Categories

LED Tape & POD strips, 5050 Professional Tape Strip Reels, Interior Tape Strip LED

UPC 811712020282

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

5050 Tape Strip Lighting

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

IP65

LUX

Product Information

Super bright, universal lighting solution for your home, office, business, or any other application • 120° viewing angle, perfect for any area • Able to be cut at 3 LED intervals (approximately every 2") for virtually any application • Maintenance free, easy installation • Improved adhesive backing for better, longer lasting application • 100,000+ hour lifetime • IP65 Water Resistant • 1 Year Warranty

Est. Labor

Hours

Gross Weight

0.60

Width

8.00

Net Weight

0.60

Height

2.00

DIM Weight

1.18

Depth

10.25

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Linear

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com