



SKU # RS-CAMO-180W

Part # 1004290

Description

32in CAMO Series CREE LED Light Bar 180W/10,700LM - While Supplies last

Categories Truck, Powersports, LED Light Bars

Sub-Categories

LED Light Bars, CAMO Series Dual Row LED Light Bars, Camouflage Dual Row Light Bars

UPC 811712027304

Unit of Measure EA

Related Skus:

Cross Sell Skus:

RSTP016

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

CAMO Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

Current Draw

Wattage

180-Watts

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

10,700lm

Beam

Pattern



Product Information

An expansion on our street series line, these camouflage style LED light bars use their camo coating to easily blend in with nature. Perfect for hunting trips or for off road vehicles. • 180W/10,700 LM (3W per diode) • Spot Style Optics • 14.2 Amps • 50,000 hour life span • 12-24v voltage range • Color Temperature: 6500K • Waterproof Certified: IP67 • Operation Temp: -40°C-80°C • Bar Measures 32" End to End w/ Brackets • Lens Measures 30" End to End • Mount to Mount measurement is 35" • Durable Camouflage Coating • 3 Year Warranty

Est. Labor

Hours

Gross Weight

10.00

Width

5.50

Net Weight

9.80

Height

6.00

DIM Weight

8.67

Depth

36.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com